# Ultra DI<sup>®</sup> 50

Liquid Optical Particle Counter

Detect process variations quickly with sensitivity down to 0.05 µm

Without measurement there is no control ®

The Ultra DI<sup>®</sup> 50 Liquid Particle Counter is designed specifically for de-ionized (DI) water systems and will count and size contaminants as small as 0.05 µm. Larger sample volumes and ultra-low zero counts detect smaller excursions with more relevant statistical data, while shorter sample intervals speed up your analysis time.

Respond immediately to contamination with real-time measurement of particles, and move quickly from one sample point to another. A low zero count, large sample volume and high counting efficiency provide you with unsurpassed performance.



# BENEFITS

#### **Rapid Analysis**

• Quickly obtain meaningful statistical data with Ultra DI 50's large sample volume

Ultra DI 50

- Save operator time with fast clean-up and the ability to move quickly from one sample point to another
- Speed up analysis time by using shorter sample intervals

#### **Process Development**

- Larger sample volumes and ultra-low zero counts detect smaller excursions with more relevant statistical data
- Respond immediately to contamination with real-time particle
  measurement
- Facility Net software provides more sophisticated process control with:
  - email notification
  - sensor status
  - tabular and SPC charts
  - time plots
  - historical event log records
- Set tighter process control limits with low sample-to-sample variation

#### Easy to Use

- Utilize existing network with Ethernet communication
- Connect directly to PLC and SCADA systems with 4-20 mA
- Compatible with ozonated water
- Stainless steel housing and dual HEPA filtration for use in clean environments

### APPLICATIONS

- Quantifying particle concentration in ultra pure water (UPW) systems
- Filter efficiency measurements
- Trending analysis at lower particle concentrations
- Detecting bacterial growth in UPW systems
- Episodic event tracking and alarming
- Continuous system monitoring
- Manufacturing process control

# Ultra DI® 50 Liquid Optical Particle Counter

## Specifications

Size range	0.05 – 0.20 μm
Channels	4
Channel sizes	0.05, 0.10, 0.15, 0.20 μm
Flow rate (ml/min)	1,000 ml/min ± 10%
Counting efficiency	100% sample volume
Sample volume	≥ 3.75 ml/min
Maximum concentration <sup>1</sup>	10,000 counts/ml
Sample temperature <sup>2</sup>	59 – 122 °F (15 – 50 °C)
Maximum pressure	100 psi
Zero count	≤ 50 counts/L
Exterior surface	Stainless steel
Wetted surface materials	Teflon®, Delrin®, fused silica, sapphire, Viton®, 96% Alumina Ceramic, and Simriz®
Dimensions (d, w, h)	17 x 17 x 10.5 in (43 x 43 x 27 cm)
Weight	45 lb (20.4 kg)
Power	100 – 240 VAC
Communications	Ethernet, 4-20 mA (3 outputs: 2 particle channels, 1 instrument status) RS-232 (set up and diagnostics only, no data)
Status indicator	Laser, power, and activity: one (1) tri-color LED
Calibration	Materials used are traceable to National Institute of Standards and Technology (NIST) and/or Japanese Industrial Standards (JIS)
Environment	Temperature: 72 – 84 °F (22 – 29 °C) ± 1 °C /hour Humidity, Non-Condensing

Greater than 90% accuracy (less than 10% coincidence loss) at the maximum recommended concentration. 1

2 For temperatures greater than 50°C, use of a chiller is recommended.

#### **HEADQUARTERS**

Boulder, Colorado 80301 USA T: +1 303 443 7100

Instrument Service & Support T: +1 303-443-7100 ext 447

Service and Calibration E: workorders@pmeasuring.com

**Technical Support** E: techsupport@pmeasuring.com

Software or System Support E: ssupport@pmeasuring.com

Customer Service and Order Processing CHINA E: customerorders@pmeasuring.com

www.pmeasuring.com info@pmeasuring.com



T: +43 171 728 285 E: pmsaustria@pmeasuring.com

BELGIUM/BENELUX T: +32 10 23 71 56 E: pmsbelgium@pmeasuring.com

BRAZIL T: +55 11 5188 8227 E: pmsbrazil@pmeasuring.com

T: +86 400 081 8020 E: pmschina@pmeasuring.com FRANCE T: +33 682 991 798 E: pmsfrance@pmeasuring.com

GERMANY T: +49 351 8896 3850 E: pmsgermany@pmeasuring.com

**IRFLAND** T: + 353 1 295 7373 E: Info.ie@pmeasuring.com

ITALY T: +39 06 9053 0130 E: pmssrl@pmeasuring.com JAPAN T: +81 44 589 3498 E: pmsjapan@pmeasuring.com

KOREA T: +82 31 286 5790 E: pmskorea@pmeasuring.com

NORDIC T: +45 7070 2855 E: pmsnordic@pmeasuring.com

PUERTO RICO T: +1 787 718 9096

T: +65 6496 0342 E: pmssingapore@pmeasuring.com

SWITZERLAND T: +41 71 987 01 01 E: pmsswitzerland@pmeasuring.com

TAIWAN T: 886-3-5525300 Ext: 301 E: pmstaiwan@pmeasuring.com

UNITED KINGDOM T: +44 (0)1223 257704 E: pmspuertorico@pmeasuring.com E: Info.uk@pmeasuring.com

For the most updated contacted information please visit <u>https://www.pmeasuring.com/contact-us/</u>



COMMITTED TO <u> 8 Net Zero</u>



Ultra DI® is a registered trademark of Particle Measuring Systems, Inc. Teflon® is a registered trademark of The Chemours Company, FC, LLC. Viton® is a registered trademark of DuPont. Defin® is a registered trademark of Defini USA LLC. Simiriz® is a registered trademark of Carl Freudenberg, KG. All other trademarks are the property of their respective owners. Particle Measuring Systems, Inc. reserves the right to change specifications without notice. © 2024 Particle Measuring Systems Inc. All rights reserved. 04172024

SINGAPORE